

# Rittal – The System.

Faster – better – everywhere.



## SV 9690.040

# Energy storage enclosure

State: 13/06/2026 (Source: [rittal.com/nz-en](http://rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9690.040 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. With flexible interior fit-out. Ideal for efficient and modular energy storage installation with slide rails.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SV 9690.040   |
| Design                            | With flexible interior fit-out  |
| Material                          | Enclosure frame: Sheet steel, 1.5 mm<br>Roof plate: Sheet steel, 1.5 mm<br>Door: Sheet steel, 1.5 mm<br>Rear panel: Sheet steel, 1.5 mm |
| Surface finish                    | Enclosure frame: Dipcoat-primed<br>Door, roof and rear panel: Powder-coated, textured paint   |
| Colour                            | RAL 7035  |
| Supply includes                   | Enclosure frame<br>Door and rear panel, perforated<br>Roof plate<br>Lock: 3 mm double-bit   |
| Protection category to IEC 60 529 | IP 20   |
| Dimensions                        | Width: 600 mm<br>Height: 2,000 mm<br>Depth: 600 mm  |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 66 kg   |
| Gross weight                      | 66.2 kg   |
| PCF per pack (cradle-to-gate)     | 208.2 kg CO2 eq (Cat B)   |
| Note on PCF category              | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                          |
| Customs tariff number             | 94032080  |
| ETIM 9                            | EC000261  |

# Features

---

Product description

VX ESS energy storage enclosure WxHxD: 600x2000x600 mm, with door, rear panel, interior fit-out

# Approvals

---

Explanations

Declaration of conformity