

Rittal – The System.

Faster – better – everywhere.



RX 9362.315

**Seccionador bajo carga para
fusibles NH**

Estado: 4/06/2025 (Fuente: rittal.com/pe-es)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.315 - Seccionador bajo carga para fusibles NH

RiLineX NH fuse-switch disconnecter in size 3 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

Características

Referencia	RX 9362.315
Ventajas	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work High rated voltage 800 V ready All variants also available with electronic fuse monitoring
Material	Poliamida (PA 6) Protección frente al fuego según UL 94 Vías de contacto: cobre electrolítico, plateado
Color	RAL 9005 RAL 35745
Unidad de envase	Connectors for electronic fuse monitoring
Para sistemas de barras con distancia entre centros	60 mm
Salida de cables	arriba/abajo
Tipo de conexión (eléctrica)	Tornillo M10
Intensidad de servicio máx.	630 A
Tensión de servicio	690 V c.a.
Para tamaño NH	3
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fusibles)

Características

Dimensiones	Anchura: 250 mm Altura: 349 mm Profundidad: 135 mm
Campo de temperatura de servicio	-5 °C...35 °C
Campo de temperatura de almacenaje	-25 °C...70 °C
Adecuado para barras colectoras	15 x 5/10 20 x 5/10 30 x 5/10
Adecuado para sistema de barras colectoras	RiLineX RiLine60
N° de polos	3 polos
Grado de suciedad	3
con control de fusibles electrónico	sí
Grado de protección IP según IEC 60 529	IP 2XB
Unidad de embalaje	1 pza(s).
Peso neto	8
Peso bruto	8
Contenido de cobre (kg / pza.)	2.255
Código arancelario	85369095
ETIM 9	EC001040