


# Rittal – The System.

Faster – better – everywhere.



## SK 3210.514

## Air/water heat exchangers

State: 07/03/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3210.514 - Air/water heat exchangers roof-mounted

For mounting on the roof surface. Cooling output 1.87 kW – 4 kW. Protection category IP 55 as standard. Particularly suitable for use in harsh environments. Flexible water connection options.



## Features

|                                          |                                                                                                                                                                                    |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                                | SK 3210.514                                                                                                                                                                        |
| Design                                   | Water-carrying parts, stainless steel (1.4571)                                                                                                                                     |
| Product description                      | For use in harsh environments and temperature ranges up to +70 °C. The air/water heat exchanger is assembled on the roof of the enclosure using flexible water connection options. |
| Colour                                   | RAL 7035                                                                                                                                                                           |
| Supply includes                          | Fully wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Sealing mat<br>Assembly parts                                                                    |
| Total cooling output                     | L 35 W 10 at 400 l/h: 3 kW                                                                                                                                                         |
| Rated operating voltage                  | 115 V, 1~, 50 Hz/60 Hz                                                                                                                                                             |
| Power consumption Pel                    | At 50 Hz: 102 W<br>At 60 Hz: 125 W                                                                                                                                                 |
| Rated current max.                       | At 50 Hz: 0.9 A<br>At 60 Hz: 1 A                                                                                                                                                   |
| Permissible operating pressure (p. max.) | 1 - 10 bar                                                                                                                                                                         |

# Features

|                                   |                                                                                                                                                                  |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type of electrical connection     | Plug-in terminal strip                                                                                                                                           |
| Duty cycle                        | 100 %                                                                                                                                                            |
| Cooling medium                    | Water (see Internet for specifications)                                                                                                                          |
| Water inlet temperature           | 1 °C...30 °C                                                                                                                                                     |
| Water connections                 | ½" connector sleeve<br>G ¾" external thread                                                                                                                      |
| Temperature control               | e-Comfort controller (factory setting +35 °C)                                                                                                                    |
| Operating temperature range       | 1 °C...70 °C                                                                                                                                                     |
| Dimensions                        | Width: 597 mm<br>Height: 417 mm<br>Depth: 475 mm                                                                                                                 |
| Note on Model No.                 | Extended delivery times.                                                                                                                                         |
| Protection category               | IP 65 available on request                                                                                                                                       |
| Pre-fuse                          | Miniature circuit-breaker/fuse: 4 A                                                                                                                              |
| Setting range                     | 20 °C...55 °C                                                                                                                                                    |
| Protection category to IEC 60 529 | IP 55                                                                                                                                                            |
| Packs of                          | 1 pc(s).                                                                                                                                                         |
| Customs tariff number             | 84158300                                                                                                                                                         |
| ETIM 9                            | EC002515                                                                                                                                                         |
| ETIM 8                            | EC002515                                                                                                                                                         |
| ECLASS 8.0                        | 27180712                                                                                                                                                         |
| Product description               | SK Air/water heat exchanger, roof-mounted, 3.0 kW, 115 V, 1~, 50/60 Hz, comfort controller, water-carrying parts: V4A (stainless steel), WHD: 597 x 417 x 475 mm |

## Approvals

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

# Tender text

## Roof-mounted air/water heat exchanger

For use in tough environments. Flexible water connection options.

Total cooling output L 35 W 10, 400l/h: 3 kW

Rated operating voltage: 115 V, 50/60 Hz

Refrigerant: Water (see specifications)

Water-carrying parts: Stainless steel (1.4571)

Dimensions [W x H x D]: 597 x 417 x 475 mm

Ambient temperature range: 1°C to 70°C

Setting range: 20°C to 55°C

Water inlet temperature range: 1°C to 30°C

Temperature control and monitoring: Comfort controller with two floating fault signal outlets and door limit switch connection (factory setting +35°C)

Type of connection: Plug-in terminal strip

Protection category to IEC 60 529: IP 55

Weight: 29.5 kg

Colour: RAL 7035