

Rittal – The System.

Faster – better – everywhere.



SK 3245.900 Blue e+ filter fan

State: 21/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3245.900 - Blue e+ filter fan with EC technology

The energy-efficient version with EC technology stands out for more than just its unique IoT capabilities. The Blue e+ fan-and-filter unit unlocks countless other advantages, from energy efficiency, to monitoring and sustainability, through to a higher air throughput (175 – 1,160 m³/h).



Features

Model No.	SK 3245.900
Design	wall-mounted EC
Benefits	Maximum air throughput via pleated filter included in the delivered state IoT link enables exclusive features such as automatic filter cleaning, filter maintenance display, emergency cooling function Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Diagonal, EC motor

Features

Air throughput, unimpeded airflow (with pleated filter)	At 50 Hz: 1,161 m ³ /h At 60 Hz: 1,161 m ³ /h
Air throughput with matching outlet filter including pleated filter	At 50 Hz: 969 m ³ /h
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 931 m ³ /h
Air throughput with matching outlet filter including chopped-fibre filter	At 50 Hz: 728 m ³ /h
Rated operating voltage	200 V - 240 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 173.5 W
Rated current max.	At 50 Hz: 1.38 A
Dimensions	Width: 323 mm Height: 323 mm Depth: 161 mm
Installation depth	141 mm
Mounting cut-out	Cut-out width: 292 mm Cut-out height: 292 mm
IP protection category to IEC 60529	IP 51 with chopped-fibre filter/pleated filter IP52 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 1, 12 with chopped-fibre filter/pleated filter Type 3, 3R with chopped-fibre filter/pleated filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...70 °C
Noise level	At 50 Hz: 72 dB(A)
Interfaces	0 - 10 V/PWM input Speed output Floating fault signal contact RS485 (ModBus)

Features

Packs of	1 pc(s).
Net weight	4,04 kg
Gross weight	4,241 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Blue e+ fan-and-filter unit, EC technology, 1161 m ³ /h, 200 V – 240 V, 1~, 50 Hz/60 Hz, WxHxD 323 x 323 x 161 mm, RAL 7035

Approvals

Approvals	CSA 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity