

Rittal – The System.

Faster – better – everywhere.



HD 1686.630 Switch housing HD

State: 04/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 1686.630 - Switch housing HD

Enclosure solution with cut-outs for switches, tailored to the requirements of the food and beverage industry. All-round gap-free silicone seal between enclosure and cover. Hygiene-compliant quick-release hexagon fastener.



Features

| | |
|--------------------------------|--|
| Model No. | HD 1686.630 |
| Design | Hygienic Design enclosure |
| Material | Enclosure and cover: Stainless steel 1.4301 (AISI 304) 1.5 mm Screw plug: Stainless steel Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 |
| Surface finish | Enclosure and cover: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010) |
| Supply includes | Enclosure of all-round solid construction Cover with switch cut-out Seal and screw plug (supplied loose) |
| Dimensions | Width front: 160 mm Width (rear): 182 mm Height, front: 220 mm Height rear: 242 mm Depth: 90 mm |
| Pitch pattern | 60 mm |
| Cut-outs (quantity x diameter) | 6 x 30.5 mm |

Features

| | |
|-------------------------------------|---|
| IK Code | IK08 |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Lock | Lock version: Hygiene-compliant quick-release hexagon fastener Number of locks: 4 |
| IP protection category to IEC 60529 | IP 66 IP X9 |
| Protection category NEMA | NEMA 1 NEMA 3 NEMA 3X NEMA 4 NEMA 4X NEMA 12 NEMA 13 |
| Type rating to UL 50E | Type 1 Type 3 Type 3X Type 4 Type 4X Type 12 Type 13 |
| Packs of | 1 pc(s). |
| Net weight | 2,1 kg |
| Gross weight | 2,153 kg |
| Customs tariff number | 84879090 |
| ETIM 9 | EC002713 |
| ETIM 8 | EC002713 |
| ECLASS 8.0 | 27180101 |
| Product description | HD switch housing, WxHxD: 160x220x90 mm, stainless steel 1.4301, 6 switch cut-outs, Ø 30.5 mm |