


Rittal – The System.

Faster – better – everywhere.



SZ 2411.801

Cable gland, brass

State: 23/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.801 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.801
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 22 mm
Thread	M12 x 1.5
Thread length	6 mm
Min. cable diameter	3 mm
Max. cable diameter	6,5 mm
Operating temperature range	-40 °C...100 °C
torque	5,5 Nm
Width across flats	14 mm
Dimensions	Thread: M12 x 1.5 Thread length: 6 mm
Type rating to UL 50E	Type 4X
Packs of	15 pc(s).
Net weight	0,195 kg
Gross weight	0,222 kg

Features

Customs tariff number	74198090
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, brass, size: M12x1,5, for cables ø 3-6.5 mm

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK
