

# Rittal – The System.

Faster – better – everywhere.



## SK 3329.104

# Wall-mounted cooling units

State: 20/07/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3329.104 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.

## Features

Model No.	SK 3329.104
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Design	wall-mounted
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0 kg
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Packs of	1 pc(s).
Net weight	68.4
Gross weight	72
EAN	4028177389434
ECLASS 8.0	27180704

## Approvals

Approvals	UL + C-UL (listed) UR + C-UR (recognized)
-----------	--

# Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK

## Tender text

Wall-mounted cooling unit Rittal TopTherm PLUS -  
NEMA 4 x, with RiNano coating and  
integral condensate evaporation  
Useful cooling output to DIN 3168 L35 L35 2500/2750 W  
Rated operating voltage 230 V, 1~, 50/60 Hz  
Power consumption Pel to DIN 3168 L35 L35 1450/1675 W  
Dimensions W x H x D [mm] 405 x 1650 x 368  
Refrigerant R 134 a  
Temperature range 20°C to 55°C (Setting range +30°C to +55°C)  
Temperature control and monitoring via  
basic controller with floating fault signal contact  
and connection for door-operated switch  
Factory setting 35°C  
Connection via pluggable terminal strip  
Protection category NEMA 4X  
Weight 83 kg  
Colour RAL 7035