

Rittal – The System.

Faster – better – everywhere.



SV 3453.500 Conductor connection clamp

State: 13/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3453.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

| | |
|---|--|
| Model No. | SV 3453.500 |
| Product description | For connecting round conductors and laminated copper bars. |
| Material | Sheet steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 16.5 x 15 mm |
| Note | Wire end ferrules should be used with fine wire conductors |
| Connection of round conductors | 35 - 70 mm ² |
| For bar thickness | 5 mm |
| Packs of | 15 pc(s). |
| Net weight | 1,515 kg |
| Gross weight | 1,62 kg |
| PCF per pack (cradle-to-gate) | 6.4 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |
| Product description | SV Conductor connection clamp, 35-70 mm ² , clamping area WH: 16,5x15 mm, for bar thickness 5 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

SV conductor connection clamps
for E-CU busbars and Rittal PLS.
For bar thickness: 5 mm
Connection of round conductors: 35 - 70 mm²
Wire end ferrules should be used with
fine wire conductors.
Clamping area: for laminated copper
bars 16.5 x 15 mm
Tightening torque
Conductor connection clamp: 10-12 Nm
Material: sheet steel, zinc-plated, passivated