

Rittal – The System.

Faster – better – everywhere.



SK 3300.120

Modular climate control concept – section door TS 8

State: 17/07/2025 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3300.120 - Modular climate control concept – section door TS 8 for installing cooling modules

Sheet steel section doors for the installation of climate control module types SK 3307.7XX to 3310.7XX.



Features

| | |
|---------------------|---|
| Model No. | SK 3300.120 |
| Product description | Sheet steel section doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Section door without preconfigured cooling module TS 8 hinges, door opening angle approx. 110° |
| Note | <p>The following information applies to 1200 mm wide TS 8 enclosures</p> <p>With the unit positioned on the right, one pack consists of a section door for installing in the right-hand half of the enclosure plus a special lockable door for the left-hand half.</p> <p>With the unit positioned on the left, one pack consists of a section door for installing in the left-hand half of the enclosure. The existing lockable door on the right may be used.</p> |
| Note on Model No. | R/h door hinge |
| To fit | Unit positioned on the right |
| To fit | Enclosure type: TS 8: = 1,200 mm: = 2,000 mm |
| Packs of | 1 pc(s). |

Features

| | |
|--------------|---------------|
| Net weight | 56.7 |
| Gross weight | 57.5 |
| EAN | 4028177560154 |
| ECLASS 8.0 | 27180702 |

Approvals

| | |
|--------------|-----|
| Certificates | EAC |
|--------------|-----|

Tender text

Modular climate control concept Section doors for installing cooling modules

Sheet steel section doors to accommodate the cooling module types SK 3307.7XX to 3310.7XX.

- Material: Sheet steel
- Colour: RAL 7035
- To fit enclosures: TS 8
- Dimensions [W x H]: 1200 x 2000 mm
- Unit positioned: on the right