## Rittal – The System.

Faster - better - everywhere.





# AS 4050.300 Assembly frame

State: 07/12/2025 (Source: rittal.com/ro-ro)



## AS 4050.300 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.

#### **Features**

Model No.	AS 4050.300		
Design	300 ENH (electrically tilt- and height-adjustable)		
Product description	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.		
Benefits	For ergonomic, back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimum space requirements during non-use Simple handling due to four castors including total lock function Variable mounting plate attachment with a quick-release fastener		
Technical specifications	Tilt adjustment approx. 0 – 80°		
Supply includes	Assembly frame 1 clamping unit pack, bottom 1 clamping unit pack, top Charger unit Battery		
Note	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.  For the USA, Canada, Central and South America and Japan, the multi-voltage power pack 4050.219 and connection adaptor 4050.222 are additionally required.		
Machine dimensions	Width: 1,400 mm Depth: 1,250 mm		
Dimensions support surface max.	Width: 1,110 mm Height: 1,900 mm		
Dimensions support surface min.	Width: 1,110 mm Height: 1,230 mm		

© Rittal 2025

#### **Features**

Load capacity	300 kg	
Working height	Working height (min.): 80 cm Working height (max.): 110 cm	
Packs of	1 pc(s).	
Net weight	230	
Gross weight	250	
Customs tariff number	84279000	
EAN	4028177804746	
ETIM 9	EC002224	
ETIM 8	EC002224	
ECLASS 8.0	36659090	

## **Approvals**

Explanations	Declaration of conformity	
--------------	---------------------------	--

© Rittal 2025 3