



AS 4050.451

Stripping machine S22

State: 23/06/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.451 - Stripping machine S22

Semi-automated machine for stripping wires of varying cross-section ranges.

Features

Model No.	AS 4050.451
Design	Touchscreen display Integral counter (total quantity) Integral counter (daily quantity) Linear adjustment of the wire stripping length
Product description	Semi-automated machine for stripping wires of varying cross-section ranges.
Benefits	Cross-section is easily set using the rotary knob Simple insertion of the wires User-friendly operation
Technical specifications	Electrically powered Wire stripping range 0.05 - 6 mm ² (AWG 30 - 10) Insulation stripping length 3 - 20 mm (0.12 - 0.79 in.) Draw-off length 3 - 20 mm (0.12 - 0.79 in.) Insertion length 22 mm (0.87 in.)
Supply includes	Stripping machine S22 Special funnel for inserting thin conductors Spare blades
Dimensions	Width: 190 mm Height: 190 mm Depth: 295 mm
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	70 VA
Cycle time	0,5 s
Packs of	1 pc(s).
Net weight	8,5 kg
Gross weight	9,06 kg

Features

Customs tariff number	84798997
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36629090
Product description	Stripping machine S 22, 0,05-6mm ²
