

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.261

### Hole punch, round

State: 20/12/2025 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.261 - Hole punch, round for sheet steel

For punching round cut-outs

## Features

Model No.	AS 4055.261
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	61,5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	1.095
Gross weight	1.169
Customs tariff number	82073010
EAN	4028177808379
ETIM 9	EC000156
ETIM 8	EC000156

# Features

ECLASS 8.0

21049047