

Rittal – The System.

Faster – better – everywhere.



VX 5301.310

Baying connector, external, 3 mm

State: 15/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.310 - Baying connector, external, 3 mm for VX IT

For baying VX IT frames with partition separation, or for replacing a pre-configured enclosure with an identical model or replacing an integral frame with a Rittal LCP cooling solution.



Features

| | |
|-------------------------------|--|
| Model No. | VX 5301.310 |
| Benefits | Supports retroactive exchange of racks or LCP devices Guarantees the required baying distance of 3 mm for carrying out retrospective modifications |
| Applications | For retrospectively exchanging racks or LCP devices For retroactive installation/removal of partitions, one-piece, slide-in |
| Material | Sheet steel |
| Surface finish | zinc-plated |
| Supply includes | 4 baying connectors, external, 3 mm Baying seal, 8 m Assembly parts |
| Note | Within a bayed enclosure suite, the external dimension is increased by 2 mm per enclosure The maximum achievable IP protection category to IEC 60 529 is IP 20. |
| To fit | Enclosure type: VX IT |
| Packs of | 4 pc(s). |
| Net weight | 0,78 kg |
| Gross weight | 0,86 kg |
| PCF per pack (cradle-to-gate) | 3.4 kg CO2 eq (Cat B) |

Features

| | |
|-----------------------|--|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002622 |
| ECLASS 8.0 | 27189263 |
| Product description | Baying connector for baying VX IT frames with partition separation, or for replacing a pre-configured enclosure with an identical model or replacing an integral frame with an LCP cooling solution. |