


Rittal – The System.

Faster – better – everywhere.



SK 3342.500

Rack-mounted fans for 482.6 mm (19")

State: 08/02/2026 (Source: ittal.com/ro-ro)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3342.500 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3342.500 |
| Product description | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Colour | RAL 7035 |
| Supply includes | Fully wired unit ready for connection Terminal strip and assembly parts |
| Air throughput (unimpeded air flow) | 480 m ³ /h |
| Note on Model No. | Rack-mounted fan for metric mounting angles available on request. Version with monitoring |
| Rated operating voltage | 115 V - 230 V, 1~, 50 Hz/60 Hz 24 V (DC) |
| Rated current max. | At 50 Hz: 0.85 A |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Dimensions | Width: 482.6 mm Height: 44 mm Depth: 200 mm |
| Distance between axes of fans | 105 mm |
| No. of fans | 3 |
| Noise level | With DC: 51 dB(A) |
| Operating temperature range | -10 °C...55 °C |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 1.8 |
| Gross weight | 1.998 |
| Customs tariff number | 84145915 |
| EAN | 4028177041530 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |

Approvals

| | |
|--------------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
| Explanations | Declaration of conformity |