


# Rittal – The System.

Faster – better – everywhere.



## DK 5301.612

# Sheet steel door, vertically divided, solid

State: 14/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5301.612 - Sheet steel door, vertically divided, solid for VX IT

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.



## Features

Model No.	DK 5301.612
Product description	To replace existing doors. The minimal rotation radius of the individual doors allows the distance between individual bayed enclosure suites to be reduced.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035 Comfort handle VX, hinges: RAL 9005
Supply includes	Door, vertically divided, with comfort handle VX for semi-cylinders with security lock 3524 E, right 3 x 180° hinges, fitted on each half of the door Assembly parts
Assembly instruction	For a door opening angle of 180° when baying, a 180° baying hinge is required

# Features

Note	Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 160°
IP protection category to IEC 60529	IP 20
To fit	Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm
Packs of	1 pc(s).
Net weight	12 kg
Gross weight	15,25 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	Sheet steel door, vertically divided, solid for VX IT, for enclosure width 800 mm, for enclosure height 2,000 mm, sheet steel, spray-finished, RAL 7035, handle and hinges: RAL 9005