Rittal – The System.

Faster – better – everywhere.





PC 5366.450 PC enclosure system

State: 29/11/2025 (Source: rittal.com/ro-ro)



PC 5366.450 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.







Features

Model No.	PC 5366.450
Design	with keyboard drawer and large mounting compartment
Product description	Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.
Material	Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Mounting compartment, support: Sheet steel
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated
General colour	RAL 7035
Colour	Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor panel, door centre part: RAL 7015

© Rittal 2025 2

Features

Supply includes	Enclosure, door, rear door
	Gland plates
	Keyboard drawer
	Mounting compartment, large
Dimensions	Width: 600 mm
	Height: 1,600 mm
	Depth: 636 mm
IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Type rating to UL 50E	Type 1
	Type 12
Max. keyboard dimensions (WxHxD)	480 x 70 x 260 mm
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	89.5
Gross weight	92
PCF per pack (cradle-to-gate)	371.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177959453
ETIM 9	EC002502
ECLASS 8.0	27180501

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity Declaration of conformity UK

Tender text

PC-Enclosure with large mounting compartment and keyboard drawer

Enclosure for stand-alone siting, consisting of solid body, large mounting compartment, keyboard drawer, bottom door, rear door and welded base assembly. Enclosure body with profiled mouting angles at the front and rear on sidewalls and roof. System slots on a 25 mm pitch pattern, all round, for individual interior installation and two pairs of mounting angles for powder-coated on the outside, textured paint Large mounting compartment: Hinged on right-hand side, at left-hand side srew-fastened from the inside, installation plate folded, decorative side trim panels Drawer for keyboard: Housing with keyboard extension piece plus pull-out

mousepad

Front trim panel with handlestrips, folded as handrest, with lock insert No.3524 E with unlocking device for glazed door, top max. keyboard dimensions (WxHxD): 480x70x260 mm Bottom door:

Vertical bars with locking rod and double-bit insert, hinged on right-hand side door resp. installation plate folded Rear door:

With locking rod and double-bit insert, hinged on right hand side With gland plates, divided Material:

© Rittal 2025

Enclosure, door, rear door, mounting compartment,

supports: Sheet steel

Handles, decorative trim panels: Plastic

Door trim panels: Aluminium

Mounting compartment, support: Sheet steel

Gland plate: Sheet steel, galvanized

Surface finish:

Enclosure and door: Dipcoat primed,

powder-coated on the outside, textured paint Mounting compartment, support: powder-coated

Colour:

Enclosure, door, decorative trim panels, supports: RAL 7035

Handle: RAL 7015

Monitor panel, door centre part: RAL 7015

Protection class:

IP to IEC 60 529: IP55

NEMA: NEMA 12

Dimensions WHD: 600 x 1600 x 636 mm

Model No.: 5366450

Manufacutrer: Rittal GmbH & Co.KG

© Rittal 2025 5