

# Rittal – The System.

Faster – better – everywhere.



## SK 3384.540

## TopTherm Blue e roof-mounted cooling unit

State: 21/08/2025 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3384.540 - TopTherm Blue e roof-mounted cooling unit

## Total cooling output 0.50 - 4.00 kW

Energy-efficient Blue e roof-mounted cooling units in output categories from 500 W to 4,000 W with e-Comfort controller integrated as standard and electrical condensate evaporation.



## Features

|                     |   |
|---------------------|---|
| Model No.           | SK 3384.540   |
| Design              | roof-mounted  |
| Product description | Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard.  |
| Benefits            | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller   |
| Material            | Sheet steel   |
| Colour              | RAL 7035  |
| Supply includes     | Condenser with hydrophobic RiNano coating<br>Integral electric condensate evaporation<br>Fully wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Assembly parts |

# Features

|  |   |
|--|---|
| Total cooling output to DIN EN 14511           | Cooling output L35 L35/50 Hz: 1.6 kW<br>Cooling output L35 L35/60 Hz: 1.75 kW<br>Cooling output L35 L50/50 Hz: 1.15 kW<br>Cooling output L35 L50/60 Hz: 1.21 kW |
| Rated operating voltage                        | 400 V, 2~, 50 Hz/60 Hz  |
| Note   | The roof-mounted cooling unit 3273.500 is also suitable for office applications, thanks to its low noise level.   |
| Rated current max.                             | At 50 Hz: 3.2 A<br>At 60 Hz: 3.8 A  |
| Start-up current max.                          | At 50 Hz: 8.7 A<br>At 60 Hz: 7.6 A  |
| Air throughput (unimpeded air flow)            | External circuit: 1,600 m³/h<br>Internal circuit: 491 m³/h  |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.3<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.92   |
| Design   | roof-mounted  |
| Dimensions                                     | Width: 597 mm<br>Height: 417 mm<br>Depth: 475 mm  |
| Protection category to IEC 60 529              | External circuit IP 34<br>Internal circuit IP 54  |
| Refrigerant/cooling medium                     | Refrigerant: R-513A<br>Quantity: 0.88 kg<br>Global Warming Potential (GWP): 631<br>CO2 equivalent (CO2e): 0.56 t  |
| Type of electrical connection                  | Plug-in terminal strip  |
| Duty cycle                                     | 100 %   |
| Temperature control                            | e-Comfort controller (factory setting +35 °C)   |
| Operating temperature range                    | 10 °C...55 °C   |
| Operating temperature max @60 Hz               | 53 °C   |
| Storage temperature range                      | -40 °C...70 °C  |

# Features

|  |  |
|--|--|
| Setting range                            | 20 °C...53 °C  |
| Power consumption Pel                    | Power consumption L35 L35/50 Hz: 0.7 kW<br>Power consumption L35 L35/60 Hz: 0.91 kW<br>Power consumption L35 L50/50 Hz: 0.79 kW<br>Power consumption L35 L50/60 Hz: 1 kW |
| Permissible operating pressure (p. max.) | 28 bar   |
| Pre-fuse                                 | Transformer circuit-breaker: 6.3...10 A  |
| Packs of                                 | 1 pc(s).   |
| Net weight                               | 54.15  |
| Gross weight                             | 57   |
| Customs tariff number                    | 84158200   |
| EAN                                      | 4028177322882  |
| ETIM 9                                   | EC000855   |
| ETIM 8                                   | EC000855   |
| ECLASS 8.0                               | 27180704   |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)<br>UL + C-UL - FT TA   |
| Certificates | EAC   |
| Explanations | Declaration of conformity<br>Declaration of conformity - F-gas regulation<br>Declaration of conformity UK |