



# AS 4052.102 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.



## Features

|                           |  |
|---------------------------|--|
| Model No.                 | AS 4052.102  |
| Design                    | Isolation protection 1000 V<br>for slot-head screws  |
| Product description       | With a long, slender handle and high-performance tip with non-transfer insulation.   |
| Benefits                  | Minimal force required, thanks to ergonomically styled handle<br>Handle head with anti-roll protection and clear screw labelling<br>Black coated blade tip to preserve precision and accuracy of fit<br>Handle 30% and insulation up to 50% slimmer than comparable tools<br>Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working |
| Material                  | Blade: Chrome-molybdenum-vanadium alloy<br>Handle core: Hard plastic<br>Handle body: Elastic, highly flexible plastic  |
| Colour                    | Handle: Anthracite and Rittal Power Pink   |
| Blade dia.                | 3,5 mm   |
| Blade length              | 100 mm   |
| Blade (width x thickness) | 3.5 x 0.6 mm   |
| Blade tip                 | SL   |
| Handle dia.               | 25 mm  |
| Handle length             | 105 mm   |

# Features

|                       |                                    |
|-----------------------|------------------------------------|
| Standards             | IEC 60 900                         |
| Packs of              | 3 pc(s).                           |
| Customs tariff number | 82054000                           |
| ETIM 9                | EC000144                           |
| ETIM 8                | EC000158                           |
| ECLASS 8.0            | 21040406                           |
| Product description   | Screwdriver insulated SL 3,5 x 0,6 |