Rittal – The System.

Faster – better – everywhere.





AS 4052.106 Screwdrivers

State: 04/11/2025 (Source: rittal.com/ro-ro)



AS 4052.106 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

Model No.	AS 4052.106	
Design	Isolation protection 1000 V for slot-head screws	
Product description	With a long, slender handle and high-performance tip with non-transfer insulation.	
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working	
Material	Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic	
Colour	Handle: Anthracite and Rittal Power Pink	
Blade dia.	5,5 mm	
Blade length	125 mm	
Blade (width x thickness)	5.5 x 1 mm	
Blade tip	SL	
Handle dia.	27 mm	
Handle length	115 mm	
Standards	IEC 60 900	
Packs of	3 pc(s).	
Customs tariff number	82054000	
EAN	4028177807235	

© Rittal 2025

Features

ETIM 9	EC000144	
ETIM 8	EC000158	
ECLASS 8.0	21040406	

© Rittal 2025 3