

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.232 Hole punch, round

State: 06/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.232 - Hole punch, round for sheet steel

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.232   |
| Design   | With 3 cutting points   |
| Supply includes                                    | Female dies<br>Male dies<br>Tension screw without ball bearing  |
| Machinable material                                | Sheet steel   |
| Maximum machinable material thickness, sheet steel | 2 mm  |
| Ø punch  | 32,5 mm   |
| For threads  | M32   |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.<br>Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number           | 4055.661  |
| Tension screw (Ø x L)                              | 9.5 x 50 mm   |
| Hydraulic tension screw Ø                          | 9,5 mm<br>19 mm   |
| Packs of   | 1 pc(s).  |
| Net weight   | 0,219 kg  |
| Gross weight                                       | 0,242 kg  |
| Customs tariff number                              | 82073010  |
| ETIM 9   | EC000156  |
| ETIM 8   | EC000156  |
| ECLASS 8.0   | 21049047  |

# Features

---

Product description

Sheet metal punch round Ø 32,5 mm