


**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.563**

**Splitter hole punch, round**

State: 23/07/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.563 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

## Features

Model No.	AS 4055.563
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	63,5 mm
For threads	M63
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.931
Gross weight	1.004
Customs tariff number	82034000
EAN	4028177808829

# Features

ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047