


# Rittal – The System.

Faster – better – everywhere.



## VX 5301.250

## Side panel, horizontally divided

State: 14/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.250 - Side panel, horizontally divided for VX IT

Side panels, horizontally divided, for VX IT

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | VX 5301.250   |
| Product description                 | For sealing IT enclosure systems, both stand-alone and baying arrangements.   |
| Benefits                            | Easy to use<br>Supports tool-free installation and removal of the side wall<br>Locked using security lock 3524 E<br>Integral internal latch |
| Material                            | Sheet steel   |
| Surface finish                      | Powder-coated   |
| Colour                              | RAL 7035  |
| Supply includes                     | Console<br>Pedestal<br>6 mounting brackets<br>2 lock components<br>Assembly parts   |
| To fit                              | Enclosure type: VX IT<br>Height: = 2,000 mm<br>Depth: = 1,000 mm  |
| IP protection category to IEC 60529 | IP 20   |
| Basic material                      | Sheet steel   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 18,1 kg   |
| Gross weight                        | 18,6 kg   |
| PCF per pack (cradle-to-gate)       | 70.9 kg CO2 eq (Cat B)  |
| Note on PCF category                | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                              |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 94039910   |
| ETIM 9                | EC002524   |
| ECLASS 8.0            | 27182101   |
| Product description   | Side panel, divided horizontally for VX IT for sealing IT enclosure systems in stand-alone or baying arrangement. For enclosure height 2,000 mm, for enclosure depth 1,000 mm. |