


Rittal – The System.

Faster – better – everywhere.



DK 7470.535

Fibre-optic splicing box with telescopic pull-out

State: 21/07/2025 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7470.535 - Fibre-optic splicing box with telescopic pull-out lockable

To accommodate splicing cassettes, optimum access thanks to telescopic pull-out.

Features

| | |
|----------------------------------|--|
| Model No. | DK 7470.535 |
| Product description | The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The rear section of the splicing box is completely open for cable entry, a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps, two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system. |
| Benefits | <p>The telescopic pull-out provides optimum access to the splicing cassettes and cable clamp</p> <p>The variable cassette fixture permits twist-proof installation of all standard splicing cassettes</p> <p>The security lock fitted at the front protects against unauthorised access</p> |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | <p>Splicing box</p> <p>Cable routing clips</p> <p>Security lock</p> <p>Cassette cover</p> <p>Mounting accessories for patch panel</p> |
| Number of splicing cassettes max | 4 |
| Note | Supplied without patch panels and splicing cassettes |
| Installation depth | 363 mm |
| Units | 2 U |

Features

| | |
|-----------------------|---------------|
| Packs of | 1 pc(s). |
| Net weight | 6.414 |
| Gross weight | 6.752 |
| Customs tariff number | 94039910 |
| EAN | 4028177167902 |
| ETIM 9 | EC001129 |
| ECLASS 8.0 | 19170113 |

Tender text

Fibre-optic splicing box for 482.6 mm installation
with telescopic pull-out, lockable, 2 U, RAL 7035

The 482.6 mm (19") splicing box is designed to accommodate splicing cassettes and can be installed in any network distributor with 482.6 mm (19") accommodation and used as a fibre-optic termination or distributor. The telescopic pull-out provides optimum access to the splicing cassettes and cable clamp. The variable cassette fixture permits twist-proof installation of all standard splicing cassettes. The security lock fitted at the front protects against unauthorised access. The rear section of the splicing box is completely open for cable entry; a rubber cable clamp strip provides protection against dust. The fibre-optic cables can be secured with cable ties or cable clamps; two strain relief clips and cable routing clips for the fibre stock provide a solution to suit any fibre-optic wiring system.

Material

sheet steel

Surface finish

RAL 7035