

Rittal – The System.

Faster – better – everywhere.



PC 5366.450 PC enclosure system

State: 05/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5366.450 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.



Features

| | |
|---------------------|---|
| Model No. | PC 5366.450 |
| Design | with keyboard drawer and large mounting compartment |
| Product description | Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access. |
| Material | Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Mounting compartment, support: Sheet steel |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated |
| General colour | RAL 7035 |
| Colour | Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor panel, door centre part: RAL 7015 |

Features

| | |
|-------------------------------------|--|
| Supply includes | Enclosure, door, rear door Gland plates Keyboard drawer Mounting compartment, large |
| Dimensions | Width: 600 mm Height: 1,600 mm Depth: 636 mm |
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Type rating to UL 50E | Type 1 Type 12 |
| Max. keyboard dimensions (WxHxD) | 480 x 70 x 260 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 89,5 kg |
| Gross weight | 92 kg |
| PCF per pack (cradle-to-gate) | 371.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002502 |
| ECLASS 8.0 | 27180501 |
| Product description | PC PC enclosure system, WHD: 600x1600x636 mm, Sheet steel, keyboard drawer, large mounting compartment |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

Approvals

Certificates

Surface finish

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

PC-Enclosure with large mounting compartment and keyboard drawer

Enclosure for stand-alone siting, consisting of solid body, large mounting compartment, keyboard drawer, bottom door, rear door and welded base assembly.

Enclosure body with profiled mounting angles at the front and rear on sidewalls and roof. System slots on a 25 mm pitch pattern, all round, for individual interior installation and two pairs of mounting angles for powder-coated on the outside, textured paint

Large mounting compartment:

Hinged on right-hand side, at left-hand side screw-fastened from the inside, installation plate folded, decorative side trim panels

Drawer for keyboard:

Housing with keyboard extension piece plus pull-out mousepad

Front trim panel with handlestrips, folded as handrest, with lock insert No.3524 E

with unlocking device for glazed door, top max. keyboard dimensions (WxHxD): 480x70x260 mm

Bottom door:

Vertical bars with locking rod and double-bit insert, hinged on right-hand side door resp. installation plate folded

Rear door:

With locking rod and double-bit insert, hinged on right hand side

With gland plates, divided

Material:

Enclosure, door, rear door, mounting compartment,
supports: Sheet steel

Handles, decorative trim panels: Plastic

Door trim panels: Aluminium

Mounting compartment, support: Sheet steel

Gland plate: Sheet steel, galvanized

Surface finish:

Enclosure and door: Dipcoat primed,
powder-coated on the outside, textured paint

Mounting compartment, support: powder-coated

Colour:

Enclosure, door, decorative trim panels, supports: RAL 7035

Handle: RAL 7015

Monitor panel, door centre part: RAL 7015

Protection class:

IP to IEC 60 529: IP55

NEMA: NEMA 12

Dimensions WHD: 600 x 1600 x 636 mm

Model No.: 5366450

Manufacturer: Rittal GmbH & Co.KG