

Rittal – The System.

Faster – better – everywhere.



SE 5850.680

VX SE free-standing enclosure system

State: 05/06/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 5850.680 - VX SE free-standing enclosure system

IP 66/NEMA 4X

Free-standing stainless steel enclosure with stable enclosure body, two integral mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible with the VX25 baying system. Efficiency is enhanced, as the side panels no longer need to be fitted. Increased protection thanks to IP 66 / NEMA 4X.



Features

| | |
|----------------|--|
| Model No. | SE 5850.680 |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed Rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed Mounting plate: Sheet steel, 3.0 mm Base: Stainless steel 1.4301 (AISI 304), 1.5 mm |
| Surface finish | Enclosure, rear panel and door: Brushed, grain size 400 Mounting plate: Zinc-plated Base: Uncoated |

Features

| | |
|-----------------------------------|--|
| Supply includes | Enclosure, solid top and sides Door(s) Door hinged on the right, may be swapped to the left Rear panel, detachable Mounting plate Base, gland plate(s) Lock: 3 mm double-bit 2 punched rails 18 x 39 mm |
| Dimensions | Width: 600 mm Height: 1,600 mm Depth: 400 mm |
| Dimensions mounting plate (W x H) | 499 mm x 1,496 mm |
| Protection category to IEC 60 529 | IP 66 |
| Protection category NEMA | NEMA 4X |
| Type rating to UL 50E | Type 1 Type 2 Type 3 Type 3X Type 3R Type 3RX Type 4 Type 4X Type 12 |
| IK Code | IK10 |
| Number of doors | 1 |
| Note | Due to the hardness of the material, we recommend using metal multi-tooth screws 2486.400 for the interior installation. |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| Packs of | 1 pc(s). |
| Net weight | 92,4 kg |
| Gross weight | 94,4 kg |
| PCF per pack (cradle-to-gate) | 283.21 |
| Customs tariff number | 94032080 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | VX SE Free-standing enclosure system, 600x1600x400 mm, Stainless Steel, 1.4301 / IP 66 / NEMA 4X, with mounting plate, single door at the front |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Certificates | Surface finish Protection category |
| Explanations | Declaration of conformity Declaration of conformity UK PCF-declaration |

Tender text

Schaltschrank (Freestanding-Enclosure VX SE IP 66/NEMA 4X)

Control cabinet for individual installation in self-supporting integral construction, consisting of basic body, door, rear panel and closed gland plate. Basic corpus made of profiled side panels and roof. Housing profile with system perforation in 25 mm DIN dimensional grid. Vertical profiles, as well as front and rear roof frame profile with two mounting levels for space-saving interior installation. Rear panel screw-fixed, Welded-in base assembly, consisting of floor frame and bottom plate with screw-fixed gland plates, Right hinged door.
Door:
with horizontal double foamed seal, with

removable square tube frame with perforation in DIN dimension grid of 25 mm, locking-rod quadruple locked, double-bit insert according to DIN 43668, hinges right hinged, changeable, with captive hinge pins, door opening angle 130° according to VDI, retrofittable to 180°, automatic potential equalization to the housing body.

Bottom plate:

One-piece base plate with gland plate, removable and exchangeable, mounted, automatic potential equalization to the housing body.

Rear panel:

with foamed seal, screwed, with square tube frame for additional reinforcement, automatic potential equalization to the housing body.

Mounting plate:

C-edged side, depth-adjustable in 25 mm grid via integrated plastic sliding pieces and reusable mounting rails.

Including mounting grid for simple positioning of components.

Material:

Housing body, door, rear panel,

Bottom plate: stainless steel 1.4301 (AISI 304)

Housing: 1.5 mm, brushed outside

Door: 2.0 mm, brushed outside

Back panel: 1.5 mm, brushed outside

Bottom plate: 3.0 mm, paint-free

Mounting plate: 3.0 mm, sheet steel

Surface:

Housing, door and rear panel: Brushed finish, grain 400

Bottom plate: paint-free

Mounting plate: galvanized

Protection class according to IEC 60 529: IP 66

Protection class according to UL 508A: Type 4X, 3R

Impact protection according to IEC 62 262: IK10

Dimensions (W x H x D): 600x1600x400 mm