Rittal – The System.

Faster – better – everywhere.





IW 6900.740 Industrial Workstations

State: 15/11/2025 (Source: rittal.com/ro-ro)



IW 6900.740 - Industrial Workstations

Lower enclosure section, based on VX SE for Industrial Workstations.







Features

Model No.	IW 6900.740
Design	Worktop, keyboard drawer, designer door, rear door
Material	Enclosure, keyboard drawer, designer door and rear door: Sheet steel
	Worktop: Chipboard (plastic-laminated on both sides (edging))
Surface finish	Enclosure: Dipcoat-primed, powder-coated on the outside, textured paint
Colour	Decorative trim panels: RAL 7015
Supply includes	Enclosure sealed at the sides
	Three-piece gland plates
	Levelling feet
	Worktop, keyboard drawer, designer door, rear door
	Worktop, W x H x D 610 x 38 x 645 mm
Dimensions	Width: 600 mm
	Height: 1,000 mm
	Depth: 645 mm
IP protection category to IEC 60 529	IP 54

© Rittal 2025

Features

Dimensions with worktop	Width: 610 mm
	Height: 1,043 mm
	Depth: 645 mm
Packs of	1 pc(s).
Net weight	71
Gross weight	74
PCF per pack (cradle-to-gate)	281.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177968547
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501

Approvals

Certificates	Surface finish
Explanations	Declaration of conformity

© Rittal 2025 3