


**Rittal – The System.**

Faster – better – everywhere.



**DK 7466.035**

**Component shelf for frame  
attachment**

State: 14/07/2025 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7466.035 - Component shelf for frame attachment

For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation, enclosure width: 600 and 800 mm, load capacity: 50 kg / 100 kg.

## Features

|                      |   |
|----------------------|---|
| Model No.            | DK 7466.035   |
| Design               | Slotted   |
| Product description  | For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation.  |
| Benefits             | Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth.<br>Mounting hole for handles provided.   |
| Applications         | For installation in enclosures without 482.6 mm (19") accommodation   |
| Material             | Sheet steel   |
| Surface finish       | Spray-finished  |
| Colour               | RAL 7035  |
| Supply includes      | Component shelf, slotted<br>2 mounting rails  |
| Installation options | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange<br>Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange<br>Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange |
| Load capacity        | 100 kg area load  |
| Assembly instruction | Additionally, two punched sections with mounting flanges are required for the inner mounting level  |
| Note                 | Max. depth of component shelves = Enclosure depth - 100 mm.   |

# Features

|                               |  |
|-------------------------------|--|
| Dimensions                    | Width: 471 mm<br>Height: 45 mm<br>Depth: 600 mm  |
| To fit                        | Enclosure type: VX<br>VX IT<br>TS IT<br>Width: 600 mm  |
| Packs of                      | 1 pc(s).   |
| Net weight                    | 7.288  |
| Gross weight                  | 7.76   |
| PCF per pack (cradle-to-gate) | 29.2 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| EAN                           | 4028177165991  |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |

# Tender text

Component shelves for 600 mm wide network enclosures

Component shelves for 600 mm wide network enclosures

Version: Max. load capacity 100 kg

Component shelves, W x D = 471 x 600 mm, 2 mm thick sheet steel version; for installing in 600 mm wide network enclosures.

The component shelf is slotted to prevent the accumulation of heat. The component shelves can hold a maximum load of 100 kg.

The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: Sheet steel

Surface finish: RAL 7035.

Dimensions: W x D: 471 x 600 mm