


Rittal – The System.

Faster – better – everywhere.



VX 8619.420

Cable clamp rail

State: 07/09/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.420 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

| | |
|--|---|
| Model No. | VX 8619.420 |
| Product description | For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth. |
| Material | Steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| VX installation options | In enclosure width 800 mm, in the base |
| VX SE installation options | In enclosure width 800 mm, in the base |
| AX installation options | In enclosure width 800 mm, in conjunction with rail for interior installation AX and base configuration rail for AX |
| AX stainless steel installation options | In enclosure width 800 mm |
| VX base/plinth installation options | In base/plinth width/depth 800 mm, in conjunction with holder/spacer |
| Installation options for VX base/plinth, stainless steel | In base/plinth width 800 mm, in conjunction with one M8 nut |
| AX base/plinth installation options | In base/plinth width 800 mm |
| To fit | Base/plinth system AX Base/plinth system VX VX base/plinth system, stainless steel |
| Dimensions | Length: 754 mm |

Features

| | |
|-----------------------|---|
| To fit | Enclosure type: VX VX SE AX CX pedestal CX one-piece console Width: = 800 mm |
| Packs of | 2 pc(s). |
| Net weight | 3.8 |
| Gross weight | 4.061 |
| Customs tariff number | 73269098 |
| EAN | 4028177921948 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |