
Rittal – The System.

Faster – better – everywhere.





VX 8619.720


Punched section with mounting flange, 14 x 39 mm


State: 12/12/2025 (Source: rittal.com/ro-ro)



VX 8619.720 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.







Features

VX 8619.720 For attaching cable ducts, cable conduit holders, equipment installed on the door, etc. Sheet steel
installed on the door, etc. Sheet steel
Zina platad
Zinc-plated
Assembly parts
475 mm
600 mm
In door width 600 mm
In door width 600 mm
In enclosure width 500 mm and in enclosure height 600 mm, in conjunction with rail for interior installation AX In enclosure width 1200 mm, in lockable door
In enclosure height 600 mm
In door width 600 mm

© Rittal 2025 2

Features

Installation options for 3-part AX	In the enclosure depth 673 mm or in the width of the wall section
PC installation options	In door width 600 mm
CX installation options	In door width 600 mm
Assembly instruction	For installation in AX sheet steel, only in conjunction with rail for interior installation AX
Note	For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required
To fit	Enclosure type: VX
	VX SE
	PC
	AX
	AX wall-mounted enclosure, 3-part
	CX one-piece console
	CX pedestal
	Suitable for width or height or depth: 600 mm
Packs of	4 pc(s).
Net weight	0.956
Gross weight	1.14
Customs tariff number	73269098
EAN	4028177924697
E-Number Sweden	E3465254
ETIM 9	EC002620
ECLASS 8.0	27189234

© Rittal 2025 3