

# Rittal – The System.

Faster – better – everywhere.



# SV 9340.270 OM supports

State: 17/04/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# SV 9340.270 - OM supports without contact system

For mounting of switchgear with external power supply.

## Features

Model No.	SV 9340.270
Design	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to-centre spacing	60 mm
Support rail type	Support frame, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0,25 kg
Gross weight	0,258 kg
Customs tariff number	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607

# Features

---

Product description

SV OM Support, WH: 55x272 mm, support frame, support rail TS 55D-V, without contact system

# Approvals

---

Approvals

ABS  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK

# Tender text

OM support (without contact system)  
OM support without contact system (3-pole)  
for busbar thickness 5/10 mm and PLS 800/1600  
Technical specifications  
Construction width: 55 mm  
Length: 272 mm  
Support frame: 55 x 237 mm  
Support frame support: yes  
PinBlock: -  
Support rail: 1  
System:  
Rittal RiLine60