

Rittal – The System.

Faster – better – everywhere.



SV 9340.270 OM supports

State: 13/05/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.270 - OM supports without contact system

For mounting of switchgear with external power supply.

Features

| | |
|---|--|
| Model No. | SV 9340.270 |
| Design | without contact system |
| Product description | For mounting of switchgear with external power supply. |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| For bar systems with centre-to-centre spacing | 60 mm |
| Support rail type | Support frame, 1 x TS 55D-V |
| Number of poles | 3-pole |
| Support frame support | Yes |
| Dimensions | Width: 55 mm Height: 272 mm |
| Support rails Qty/height | 1 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Support frame (W x H) | 55 mm x 237 mm |
| Approvals | UL |
| Packs of | 1 pc(s). |
| Net weight | 0,25 kg |
| Gross weight | 0,258 kg |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001166 |
| ECLASS 8.0 | 27400607 |

Features

| | |
|---------------------|--|
| Product description | SV OM Support, WH: 55x272 mm, support frame, support rail TS 55D-V, without contact system |
|---------------------|--|

Approvals

| | |
|-----------|---|
| Approvals | ABS DNV Lloyds Register UL + C-UL (listed) |
|-----------|---|

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|

Tender text

OM support (without contact system)
OM support without contact system (3-pole)
for busbar thickness 5/10 mm and PLS 800/1600
Technical specifications
Construction width: 55 mm
Length: 272 mm
Support frame: 55 x 237 mm
Support frame support: yes
PinBlock: -
Support rail: 1
System:
Rittal RiLine60