

**Rittal – The System.**

Faster – better – everywhere.



**SV 9340.950**

**Bus-mounting fuse base D-Switch**

State: 11/07/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

## Features

Model No.	SV 9340.950
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035 Fuse holder: RAL 7001
Supply includes	Retaining springs for D 01 and 10 x 38 mm fuses
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to-centre spacing	60 mm
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors up to 6 mm <sup>2</sup>
Type of electrical connection	Box terminal
Fuse inserts	D 01 (with reducer) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring)
Fuse inserts footnote	When using D 01 and 10 x 38 mm fuses, reducers must be used. Use of D 01 fuses optionally possible with adaptor sleeve for D 02 base/plinths.
Rated operating current max.	63 A
Rated operating voltage	400 V
Test specification	IEC/DIN EN 60 947-3
Dimensions	Width: 27 mm Height: 226 mm
Connection of round conductors	1.5 - 25 mm <sup>2</sup>

# Features

To fit busbars	Height: 5, 10 mm
Voltage range for indicator lights	100 - 400 V
Number of poles	3-pole
Round conductor cross-section	1.5 - 25 mm <sup>2</sup>
Packs of	3 pc(s).
Net weight	0,975 kg
Gross weight	1,04 kg
Copper weight (kg per piece)	0,066
Customs tariff number	85369095
ETIM 9	EC001046
ECLASS 8.0	27371402
Product description	SV Bus-mounting fuse base, D-Switch, 63 A, 400 V, 3-pole, round conductor connection 1,5-25 mm <sup>2</sup>

# Approvals

Explanations

Declaration of conformity