## Rittal - The System.

Faster – better – everywhere.





# RX 9360.612 RiLineX CB component adaptor

State: 24/10/2025 (Source: rittal.com/ro-ro)



## RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



#### **Features**

Model No.	RX 9360.612
Design	universal
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar
	thickness 5/10 mm
	Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6)
	Fire protection corresponding to UL 94
Colour	RAL 9005
	RAL 35745
Supply includes	3 connection space covers
IP protection category to IEC 60 529	IP 2XB
Rated impulse withstand voltage Uimp	12 kV
Rated voltage	690 V AC
	690 V DC
	600 V AC (UL)

© Rittal 2025

## **Features**

Rated insulation voltage	1.000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Bottom
Type of electrical connection	Screw M8
To fit manufacturer (model)	ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW1603P, BW2503) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX³ 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Schneider (EZC250H,NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250)
To fit busbar system	RiLineX RiLine60
Fundamental frequency	5060 Hz
Ambient humidity (non- condensing)	1090 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C55 °C
Storage temperature range	-25 °C75 °C

© Rittal 2025 3

### **Features**

Dimensions	Width: 105 mm Height: 252 mm Depth: 63 mm
Packs of	1 pc(s).
Net weight	1.472
Gross weight	1.474
Copper weight (kg per piece)	0.608
Customs tariff number	85369095
EAN	4028177997080
ETIM 9	EC001531

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025