Rittal - The System.

Faster – better – everywhere.





RX 9360.625 RiLineX CB component adaptor

State: 28/11/2025 (Source: rittal.com/ro-ro)



RX 9360.625 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 400 A) for 60 mm busbar systems. The device width is 145 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Model No.	RX 9360.625
Design	universal
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	Including 3 connection space covers, 2 cross members and assembly parts
IP protection category to IEC 60 529	IP 2XB
Rated impulse withstand voltage Uimp	12 kV

© Rittal 2025 2

Features

Rated voltage	690 V AC 690 V DC
	600 V AC (UL)
Rated insulation voltage	1.000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Screw M10
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
To fit busbar system	RiLineX RiLine60
Fundamental frequency	5060 Hz
Ambient humidity (non-condensing)	1090 %
To fit busbars	15 x 5/10
	20 x 5/10
	30 x 5/10
Operating temperature range	-25 °C55 °C
Storage temperature range	-25 °C75 °C
Dimensions	Width: 145 mm
	Height: 325.8 mm
	Depth: 76.4 mm
Packs of	1 pc(s).
Net weight	3.6
Gross weight	3.8
Copper weight (kg per piece)	1.652
Customs tariff number	85369095
EAN	4028177997073

© Rittal 2025 3

Features

ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)	
Explanations	Declaration of conformity	

© Rittal 2025