

Rittal – The System.

Faster – better – everywhere.



VX 8660.090

Base/plinth trim panels, vented

State: 01/07/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.090 - Base/plinth trim panels, vented for base/plinth system VX, sheet steel

For venting the enclosure via the base/plinth. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. Thanks to the optional trim panel attachment, the vented trim panels may also be fitted at the side of the base/plinth corner piece.

Features

| | |
|-----------------------|---|
| Model No. | VX 8660.090 |
| Design | Vented |
| Material | Sheet steel |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Dimensions | Height: 100 mm |
| To fit | Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width/depth: 600 mm |
| Type rating to UL 50E | Type 1 Type 12 |
| Weight/pack | 1,42 kg |
| Packs of | 2 pc(s). |
| To fit | for base/plinth system VX, sheet steel |
| Net weight | 1 kg |
| Gross weight | 1,319 kg |

Features

| | |
|-------------------------------|---|
| PCF per pack (cradle-to-gate) | 17.01 |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX base/plinth trim panel, vented, for W/D: 600 mm, sheet steel |

Approvals

| | |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|