

**Rittal – The System.**

Faster – better – everywhere.



# SV 9665.770

## Cable entry gland

State: 23/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9665.770 - Cable entry gland for roof plate

Cable entry glands for roof plates, with metric knockouts, sealing membranes, entry glands, or sealed.



## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | SV 9665.770   |
| Design                              | with sealing membranes 32 x Ø 7 – 16 mm, 4 x Ø 10 – 20 mm, 3 x Ø 14 – 26 mm |
| Product description                 | For simple, secure cable entry in the roof zone.                            |
| Material                            | Insulating material   |
| Colour                              | RAL 7035  |
| Supply includes                     | Seal included   |
| Dimensions                          | Width: 250 mm<br>Depth: 160 mm  |
| IP protection category to IEC 60529 | IP 55   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 0,3 kg  |
| Gross weight                        | 0,341 kg  |
| Customs tariff number               | 39269097  |
| ETIM 9                              | EC000211  |
| ECLASS 8.0                          | 27142421  |

# Features

---

Product description

SV Cable entry gland, with sealing membranes, 32x Ø 7-16 mm, 4x Ø 10-20 mm, 3x Ø 14-26 mm, insulating material