



# SV 9344.000 - NH fuse-switch disconnecter

## Features

|   |   |
|---|---|
| Model No.                               | SV 9344.000   |
| Design                                  | For mounting plate assembly   |
| Material                                | Polyamide<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated             |
| Colour                                  | Chassis: RAL 7035<br>Cover: RAL 7035/7001   |
| Clamping area for laminated copper bars | Clamping area width: 13 mm<br>Clamping area height: 13 mm   |
| for mounting plate assembly             | Yes   |
| Cable outlet                            | Top/bottom  |
| Type of electrical connection           | Box terminal  |
| Rated operating current max.            | 160 A   |
| Rated operating voltage                 | 690 V, 3~   |
| For NH size                             | 00  |
| Note                                    | The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses". |
| Test specification                      | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)   |
| Dimensions                              | Width: 106 mm<br>Height: 194 mm   |
| Connection of round conductors          | 4 - 95 mm <sup>2</sup>  |
| Number of poles                         | 3-pole  |
| Round conductor cross-section           | 4 - 95 mm <sup>2</sup>  |
| Packs of                                | 1 pc(s).  |
| Net weight                              | 0,7 kg  |

## Features

---

|                              |  |
|------------------------------|--|
| Gross weight                 | 0,74 kg  |
| Copper weight (kg per piece) | 0,15   |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC000249   |
| ECLASS 8.0                   | 27371401   |
| Product description          | SV NH fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, box terminal, for mounting plate assembly |

## Approvals

---

|              |   |
|--------------|---|
| Approvals    | C-UR<br>CQC-CCC<br>UR + C-UR (recognized)                 |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |