


Rittal – The System.

Faster – better – everywhere.



RX 9360.710

RiLineX component adaptor

State: 14/08/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.710 - RiLineX component adaptor

RiLineX component adaptor (16 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



Features

| | |
|------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | RX 9360.710 |
| Design | With connection cable |
| Benefits | For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Simple assembly Coordinated accessories reduce the number of different items required |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 RAL 35745 |
| Connection cables (AWG) | AWG 14 |
| Rated current max. | 16 A |
| Electrical ratings UL (SCCR) | 5 kA - 600 V, RMS 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7 |
| Cable outlet | Top |

Features

| | |
|-----------------------------------------------|------------------------------------------------|
| For bar systems with centre-to-centre spacing | 60 mm |
| Length of connection cable | 150 mm |
| Number of poles | 3-pole |
| To fit busbar system | RiLineX RiLine60 |
| Dimensions | Width: 45 mm Height: 240 mm Depth: 37 mm |
| Support rails Qty/height | 1 / 10 mm |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rated voltage | 690 V AC 600 V AC (UL) 600 V DC (UL) |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC 61 439-1/-2 UL 508 |
| IP protection category to IEC 60 529 | IP 2XB |
| Operation humidity max | 90 % |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Packs of | 4 pc(s). |
| Net weight | 1.2 |
| Gross weight | 1.35 |
| Copper weight (kg per piece) | 0.108 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177997035 |
| ETIM 9 | EC001531 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |