

Rittal – The System.

Faster – better – everywhere.



RX 9360.805 Bus-mounting fuse base

State: 08/06/2025 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.805 - Bus-mounting fuse base

Bus-mounting fuse base for RiLineX and 60 mm busbar systems. For slow fuse D01 (with gauge ring) and D02 (E18). With electronic and optical LED fuse monitoring via alarm contacts. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm² at angle of 45° enables easier conductor connection. The device is suitable for tool-free snap-on mounting and has semi-automatic rail adjustment for 5 and 10 mm.



Features

| | |
|-----------------|--|
| Model No. | RX 9360.805 |
| Design | with electronic fuse monitoring |
| Benefits | Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps) |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94-V0 |
| Colour | RAL 35745 RAL 9005 |
| Supply includes | 4 bus-mounting fuse bases 12 reducers for D 01 fuses |
| Cable outlet | Bottom |
| Number of poles | 3-pole |

Features

| | |
|--|---|
| To fit busbar system | RiLineX RiLine60 |
| Dimensions | Width: 36 mm Height: 263 mm Depth: 123.5 mm |
| Connection of round conductors, fine wire with wire end ferrule | 1.5 - 16 mm ² |
| Connection of round conductors, fine wire with AWG wire end ferrule | AWG 16 - AWG 6 |
| Connection of round conductors, multi-wire | 1.5 - 16 mm ² |
| Connection of round conductors, multi-wire mm ² | AWG 16 - AWG 6 |
| To fit busbars | Height: 5, 10 mm |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rated voltage | 400 V AC |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC/DIN EN 60 947-3 |
| Rated insulation voltage | 1.000 V |
| Power dissipation (max.) | 5,5 W |
| IP protection category to IEC 60 529 | IP 2XB |
| Operation humidity max | 90 % |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non- condensing) | 10...90 % |
| Utilisation category | AC-21B (400 V/100 A) |

Features

| | |
|------------------------------|----------|
| Packs of | 4 pc(s). |
| Net weight | 1.796 |
| Gross weight | 1.8 |
| Copper weight (kg per piece) | 0.07 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001644 |