

Rittal – The System.

Faster – better – everywhere.



SG 2372.102

Signal pillar 3-way LED

State: 02/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.102 - Signal pillar 3-way LED

Identify malfunctions and operating statuses in machines and automated processes immediately with Rittal's flexible range of signal pillars to suit all applications. If you only need three standard signal colours, the plug-and-play 3-way LED signal system is the ideal choice.

Features

Model No.	SG 2372.102
Design	for wall/base mounting
Benefits	Complete, ready-to-connect solution Extremely long service life of the LEDs (max. 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs
Technical specifications	3-stage, red, yellow, green Transmission angle: 3 x 120°
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Type of electrical connection	Screwless spring terminals
Light	LEDs
Dimensions	Height: 211.5 mm
Operating temperature range	-20 °C...50 °C
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V
Thread	M12 x 1.5
Note	The signal pillar is comprised of items 2372001, 2372021, 2372011 and 2368002
Packs of	1 pc(s).
Net weight	0,25 kg
Gross weight	0,309 kg
Customs tariff number	85318070

Features

ETIM 9	EC001042
ETIM 8	EC001042
ECLASS 8.0	27371230
Product description	SG signal pillar, LED compact for wall mounting

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------
