

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.232

# Current measurement module

State: 05/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.232 - Current measurement module

To extend the modular network analyser REM 801 with 8 additional current measurement channels.

## Features

|   |  |
|---|--|
| Model No.   | SV 9393.232  |
| Design  | REM 800-CT-8-LP<br>null  |
| Product description   | To extend the modular network analyser REM 801 to a maximum of 92 current measuring channels or for connecting remote system parts etc. Up to 10 extension modules, such as current measurement modules with a maximum bus length of 100 m, may be connected via the internal bus or the bus connection modules. |
| Operating temperature range   | -10 °C...55 °C   |
| Storage temperature range   | -25 °C...70 °C   |
| Ambient humidity (non-condensing)                                       | 5...95 %   |
| IP protection category to IEC 60529                                     | IP 20  |
| For mounting on support rails   | Yes  |
| Current measurement inputs  | 8 (2x4)<br>2 systems – L1, L2, L3, N<br>Individual channels  |
| Measurement by way of low-power current transformer (secondary voltage) | 0...0.4 V  |
| Fundamental frequency   | 40...70 Hz   |
| Harmonic  | 1...15   |
| Packs of  | 1 pc(s).   |
| Net weight  | 0,29 kg  |
| Gross weight  | 0,295 kg   |

# Features

---

|                       |  |
|-----------------------|--|
| Customs tariff number | 85389099   |
| Product description   | SV Current measurement module REM 800-CT-8-LP for secondary current converters |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|