


# Rittal – The System.

Faster – better – everywhere.



## SV 9666.340 Connection terminal block

State: 07/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9666.340 - Connection terminal block

For connecting copper and aluminium conductors as well as laminated copper bars.

## Features

|   |   |
|---|---|
| Model No.                                       | SV 9666.340   |
| Product description                             | For connecting copper and aluminium conductors. For laminated copper bars or solid and stranded conductors with a pressed wire end ferrule.         |
| Material  | Duroplastic   |
| Colour  | RAL 7035  |
| Supply includes                                 | Assembly parts  |
| Assembly instruction                            | Contact hazard protection module 9666.020 is additionally required to cover the connection terminal block.  |
| Rated current max.                              | 250 A   |
| Number of poles                                 | 5-pole  |
| Connection of round conductors                  | 16 - 150<br>2 x 16 - 70   |
| Clamping area for laminated copper bars (W x H) | 17 x 21 mm  |
| Packs of  | 1 pc(s).  |
| Net weight                                      | 3,013 kg  |
| Gross weight                                    | 3,213 kg  |
| Customs tariff number                           | 39211900  |
| ETIM 9  | EC001894  |
| ECLASS 8.0                                      | 27400613  |
| Product description                             | SV Connection terminal block (ISV), 250 A, 690 V, 5-pole, round conductor connection, 1x16-150/2x16-70 mm <sup>2</sup> , clamping area BH: 17x21 mm |

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK