


Rittal – The System.

Faster – better – everywhere.



VX 9666.966

Bayed enclosure system VX25

State: 09/04/2026 (Source: rittal.com/ro-ro)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9666.966 - Bayed enclosure system VX25 Distribution enclosure

Baying systems VX as distribution enclosures, prepared for ISV installation modules



Features

Model No.	VX 9666.966
Material	Sheet steel
Surface finish	Enclosure frame: Dipcoat-primed Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Gland plates Rear panel Roof plate Lock: 3 mm double-bit
Number of doors	2
Note	For 600 mm wide distribution enclosures, please use VX basic enclosures For a base/plinth height of 200 mm, 2 packs each of plinth corner pieces, 100 mm and base/plinth trim panels, 100 mm are required

Features

IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Test specification	IEC 61 439-1/-2
Dimensions	Width: 1,100 mm Height: 2,000 mm Depth: 400 mm
Packs of	1 pc(s).
Net weight	111,65 kg
Gross weight	118,6 kg
PCF per pack (cradle-to-gate)	359.7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC000214
ECLASS 8.0	27142409
Product description	VX Distribution enclosure (ISV), WHdepth 1100x2000x400 mm, sheet steel, two-door

Approvals

Approvals	Bureau Veritas DNV-GL
Certificates	Surface finish
Explanations	Declaration of conformity UK