

Rittal – The System.

Faster – better – everywhere.



SV 3586.020 CUPONAL busbars

State: 02/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3586.020 - CUPONAL busbars

Copper-coated aluminium busbar



Features

| | |
|------------------------------|---|
| Model No. | SV 3586.020 |
| Product description | Copper-coated aluminium busbars, suitable for configuring busbar systems with busbar supports 9340.000/9340.050. |
| Material | Aluminium Copper |
| Rated current max. | 493 A |
| Note | The rated current is derived at 65 °C bar temperature and 35 °C ambient temperature Correction factor diagram to DIN EN 43 671 May be cut individually to required length |
| Standards | DIN EN 13 601 |
| Cross-section | 30 mm x 10 mm |
| Dimensions | Length: 2,400 mm |
| Packs of | 3 pc(s). |
| Net weight | 7,5 kg |
| Gross weight | 9,2 kg |
| Copper weight (kg per piece) | 1,05 |
| Customs tariff number | 74071000 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC001522 |
| ETIM 8 | EC001522 |
| ECLASS 8.0 | 27370303 |
| Product description | SV Busbar CUPONAL, WH: 30x10 mm, L: 2400 mm |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|