

Rittal – The System.

Faster – better – everywhere.



AS 4054.030 Flex crimping tool

State: 02/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.030 - Flex crimping tool for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.



Features

Model No.	AS 4054.030
Design	Straight
Product description	For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.
Benefits	Front or side accommodation of the wire end ferrule with a rotatable head Minimal effort required with large wire cross-sections Uniformly high quality compression Releasable ratchet Self-adjusting
Material	High-quality special tool steel
Surface finish	Coated, black, matt
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Trapezoid crimp
Direction of cable entry	front and side
Dimensions	Length: 180 mm
AWG	26 - 8
For cross-section	0.14 - 10 mm ²
Packs of	1 pc(s).

Features

Net weight	0,35 kg
Gross weight	0,388 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	AS crimping tool for cross-section 0.14 – 10 mm ² , rotating head, trapezoidal crimp