

# Rittal – The System.

Faster – better – everywhere.



## SK 3303.508

# TopTherm wall-mounted cooling unit Blue e, UL Type 3R/4

State: 22/06/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3303.508 - TopTherm wall-mounted cooling unit

## Blue e, UL Type 3R/4 0.5 - 2.5 kW

Energy-efficient Blue e wall-mounted cooling units in output categories 500 W to 2,500 W with integral e-Comfort controller and electric condensate evaporation (from 1000 W) as standard, protection category UL Type 3R/4, 12.



## Features

Model No.	SK 3303.508
Design	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category UL Type 3R/4, 12.
Benefits	Suitable for outdoor siting Blue e technology May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts

# Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.44 kW Cooling output L35 L35/60 Hz: 0.5 kW Cooling output L35 L50/50 Hz: 0.23 kW Cooling output L35 L50/60 Hz: 0.32 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Note on Model No.	without integral condensate evaporation
Rated current max.	At 50 Hz: 2.6 A At 60 Hz: 2.6 A
Start-up current max.	At 50 Hz: 5.1 A At 60 Hz: 6.4 A
Air throughput (unimpeded air flow)	External circuit: 315 m <sup>3</sup> /h Internal circuit: 265 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.13 Refrigeration factor L35 L35 (EER) 60 Hz: 1.22
Design	wall-mounted
Dimensions	Width: 285 mm Height: 620 mm Depth: 298 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 56
Protection category NEMA	UL Type 3R UL Type 4 UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.17 kg Global Warming Potential (GWP): 631 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.11 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	-20 °C...50 °C
Operating temperature max @60 Hz	50 °C
Operating temperature	Compressor cooling mode from +10 °C ambient temperature. Only the internal fan is active in the temperature range -20 °C to +10 °C.

# Features

Storage temperature range	-40 °C...70 °C
Setting range	20 °C...50 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.35 kW Power consumption L35 L35/60 Hz: 0.41 kW Power consumption L35 L50/50 Hz: 0.45 kW Power consumption L35 L50/60 Hz: 0.48 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
Net weight	28,5 kg
Gross weight	38,5 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK Blue e cooling unit, wall-mounted, UL Type 3R/4, 0.44 kW, 230 V, 1~, 50/60 Hz, sheet steel, WHD: 285 x 620 x 298 mm

# Approvals

Approvals	C-UL UL + C-UL (listed) UL + C-UL - FTTA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK