



# CP 6380.000 - Optipanel

Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Super-slimline design, needs hardly more space than the installed equipment itself.



## Features

|                 |  |
|-----------------|--|
| Model No.       | CP 6380.000  |
| Design          | Support arm connection, rectangular 120 x 65 mm  |
| Benefits        | Aluminium enclosure, high thermal conductivity for optimum passive heat dissipation.<br>Low weight coupled with high stability<br>Compatible with all Rittal stand and support arm systems |
| Material        | Enclosure: Extruded aluminium section<br>Corner pieces: Die-cast zinc<br>Corner protectors: Plastic  |
| General colour  | Natural anodised   |
| Colour          | Enclosure: Natural anodised<br>Corner pieces: RAL 7035<br>Corner protectors: similar to RAL 7024   |
| Supply includes | Enclosure with hinged rear panel<br>Seals  |
| Dimensions      | Width: 526.6 mm<br>Height: 354.3 mm<br>Depth: 110 mm   |

# Features

|                                     |   |
|-------------------------------------|---|
| Installation depth                  | 100 mm  |
| IP protection category to IEC 60529 | IP 65   |
| To fit front panel width            | 482,6 mm  |
| To fit front panel height           | 310,3 mm  |
| Design                              | Servicing access from the rear  |
| Note                                | The support arm connection may be swapped over by rotating the enclosure<br>3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C<br>Hinging of the rear panel on the longest enclosure side |
| Basic material                      | Aluminium   |
| Lock                                | Lock version: Cam<br>Number of locks: 2<br>Lock insert: 3 mm double-bit   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 5,86 kg   |
| Gross weight                        | 6,168 kg  |
| Customs tariff number               | 94032080  |
| ETIM 9                              | EC002504  |
| ECLASS 8.0                          | 27180505  |
| Product description                 | CP Optipanel, for front panel BH 482,6x310,3 mm, installation depth 100 mm, Extruded aluminum section, Support arm connection 120x65 mm   |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |