

# Rittal – The System.

Faster – better – everywhere.



## DK 7480.035

## Energy-Box, 482.6 mm (19")

State: 11/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7480.035 - Energy-Box, 482.6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1 – 3 , maximum accommodation of 22 items of installed equipment.

## Features

Model No.	DK 7480.035
Product description	Depth-variable top hat rail for installed equipment to DIN 43 880 in sizes 1 – 3, e.g. to accommodate flush-type socket outlets, circuit-breakers, etc., with cable clamping at the rear and one N and one PE rail each on an insulated base/plinth.
Colour	RAL 7035
Supply includes	Energy-Box with depth-variable top hat rail for installed equipment to DIN 43880, sizes 1 – 3, with brush strip for cable entry at the rear Plastic hood including extension cover (UL94-V0) 44 connection clamps, 4 mm <sup>2</sup> 2 connection clamps, 16 mm <sup>2</sup> 2 blanking covers 12 clips for strain relief of the connection cables Identification strips, self-adhesive
Max. pitch units @ 18 mm	22
Note	Individual population with circuit-breakers at the factory available on request.
Dimensions	Width: 482.6 mm Height: 132.5 mm Depth: 155 mm
Units	3 U
Packs of	1 pc(s).
Net weight	2,354 kg
Gross weight	2,54 kg
Customs tariff number	85366990
ETIM 9	EC002620

# Features

---

ECLASS 8.0

27189261

---

Product description

DK Energy-Box, WHD: 482,6 (19")x132,5x155 mm, max. 22 pitch units

## Tender text

Energy-Box, 3 U,  
with adjustable top-hat rail for installed equipment as per  
DIN 43880 in sizes 1 - 3. A cable clamp is integrated  
in the box. One N and one PE rails are already fitted  
on isolated bases. The plastic cover, which includes an  
extension cover (UL 94-V0), can hold a maximum of 22 pieces of  
installed equipment (width = 18 mm).

Supply includes:

1 pcs. Energy-Box with depth adjustable top hat rail for installation  
equipment to DIN 43880, sizes 1-3, maximum 22 HP, including mounted N-  
and PE-rail on isolated base.

Within a brush strip on the backside for cable entry

1 pcs. plastic hood incl. extension cover (UL-94-V0)

44 pcs. connection clamps, 4 mm<sup>2</sup>

2 pcs. connection clamps, 16 mm<sup>2</sup>

2 pcs. blanking cover

12 pcs. clips for cable strain relief

Identificationstrips, self-adhesive