

Rittal – The System.

Faster – better – everywhere.



DK 7816.360

Sheet steel door, vertically divided,
solid

State: 18/03/2026 (Source: m/rs-s)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7816.360 - Sheet steel door, vertically divided, solid for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

Model No.	DK 7816.360
Product description	With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.
Material	Sheet steel
Supply includes	Assembly parts
Note on Model No.	Without tubular door frame. Tubular door frame available on request.
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: DK-TS Width: 600 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	26,6 kg
Gross weight	28 kg
Customs tariff number	94032080
ETIM 9	EC000747
ECLASS 8.0	27182204

Tender text

Sheet steel door, vertically divided for TS

W x H = 600 x 2000 mm

Sheet steel door with 130° hinges and assembly parts,
locking rod including comfort handle for semi-cylinder
with 3524 E security lock.

Non-vented sheet steel door.

Material: Sheet steel, spray finished in RAL 7035

For 600 mm x 2000 mm enclosures