

Rittal – The System.

Faster – better – everywhere.



AS 4055.070

**Manual hydraulic punch set, M16 -
M63**

State: 02/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.070 - Manual hydraulic punch set, M16 - M63

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

Features

Model No.	AS 4055.070
Design	This set includes the standard hole punches M16 to M63
Product description	Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in overpressure valve Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel
Supply includes	Manual hydraulic punch, straight 7 splitter hole punches, triple splitting Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 10 mm Spacer sleeve set (3-part) Plastic case
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø punch	16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm 50,5 mm 63,5 mm

Features

For threads	M16 M20 M25 M32 M40 M50 M63
Packs of	1 pc(s).
Net weight	5,3 kg
Gross weight	5,34 kg
Customs tariff number	82034000
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046
Product description	Hand hydraulic punch set straight M16,20,25,32,40,50,63 mm
